



VVA402N

by Burndy
Catalog ID: VVA402N

Prop 65 Notice

Cast Cu Alloy Varilugs, 2 Holes, 800-500 KCML, 230 kV, 7.69 IN L, 0.56 Bolt Hole Dia

Product Details

General

Application	Substation
Clamping Element Design	V Bolt
Connector Type	Terminal
Installation Torque Recommended in-lb	500 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Clamping Elements	2
Physical Attribute - Number of Holes	2
Physical Attribute - Pad Alignment	Offset
Physical Attribute - Pad Configuration	1.62 x 3 - 2 holes
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Trade Name	VARILUG™
Type	Bolted Lugs & Terminals
UPC	781810005736
UPC 12 Digit	7818100057366

Dimensions

Dimension - B Length inch	1.34 in
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.88 in
Dimension - Hole Size fraction	9/16
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	195 mm
Dimension - Length Overall inch	7.69 in
Dimension - N inch	0.62 in

Dimension - Pad Size inch	1.62 x 3
Dimension - Pad Width inch	1.62 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Flat
Conductor - Copper Str Size	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Size Range	500 kcmil-800 kcmil
Conductor Type	CU C Str-Size
Number Of Conductors	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)