



WAD1015

by Burndy
Catalog ID: WAD1015

Prop 65 Notice

MAX RANGE: .398 - .502 ACSR: 1/0 (6/1), 2/0 (6/1), 3/0 (6/1) AAC: 1/0, 2/0, 3/0 15 kV, 110 BIL

Product Details

General

| | |
|-------------------------------|---------------|
| Insulator Type | Silicon |
| Rating - Body Strength | 10000 lbs |
| Rating - Pulling Eye Strength | 6000 lbs |
| Trade Name | WEJTAP™ |
| UPC | 781810560488 |
| UPC 12 Digit | 7818105604888 |

Electrical Ratings

| | |
|----------------|-------|
| Current Rating | 900 A |
|----------------|-------|

Conductor Related

| | |
|----------------------------------|--|
| Conductor - AAAC 5005 Size | 30.58 (7) kcmil |
| Conductor - AAAC 5005 Size Range | 30.58 (7) kcmil |
| Conductor - AAAC 6201 Size | 30.58 (7) kcmil |
| Conductor - AAAC 6201 Size Range | 30.58 (7) kcmil |
| Conductor - ACSR Str Size | 1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG |
| Conductor - ACSR Str Size Range | 1 (6/1) Robin AWG-3/0 (6/1) Pigeon AWG |
| Conductor - AL Str Size | 1/0 AWG;2/0 AWG;3/0 AWG |
| Conductor - AL Str Size Range | 1/0 AWG-3/0 AWG |
| Conductor Type | <ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | UI |
| UL Listed | No |

Logistics

| |
|-----------------------|
| Minimum Pack Quantity |
|-----------------------|

| |
|---|
| 1 |
|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)