



WCB14

by Burndy
Catalog ID: WCB14

Prop 65 Notice

Wejtap Assembly , Installed With Blue Booster,Run:.568-.364,
Tap:.398-.257.

Features: WEJTAP Connectors Use An Aluminum Alloy Wedge That Is Power-Driven Between The Run And The Tap Cables Locking Them Into A C Shaped Tempered Aluminum Alloy Spring-Body, The Spring-Body Maintains Consistent Pressure Throughout The Life Of The Connection To Ensure Reliability During Severe Electrical And Climatic Conditions, The Wedges Wiping Action Combined With Factory Installed PENTX 1530 Provides Superior Contact Integrity, The Wedge Is Automatically Locked Onto The Spring-Body By A Skiving Action Produced By A Lance At The Forward End Of The WEJTAP Installation Tool, Conductor Type: Run: AAC, Tap: AAC, Copper, Cable Diameter Range: 0.839 - 0.690 IN, Cable Diameter Range (run): 0.568 - 0.364 IN, Cable Diameter Range (tap): 0.398 - 0.257 IN, Conductor Size (run - Mm): 9 - 14 SQ-MM, Conductor Size (tap - Mm): 7 - 10 SQ-MM, Installation Tool: WTRB, Booster: WPBB Box 25, Color Code: Blue

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872659
UPC 12 Digit	7818108726599

Dimensions

Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in

Conductor Related

Conductor - ACSR Str Run	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap	4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Tap Range	3 AWG-1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)