



WCB20

by Burndy
Catalog ID: WCB20

Prop 65 Notice

Wejtap Assembly , Installed With Blue Booster,Run:.568-.364,
Tap:.572-.386.

Features: With Blue Power Booster, ANSI Class AA, Installation Tool:
WTRB Tool, Color Code: Blue, Conductor Size (tap - Mm): 10 - 12 SQ-MM,
Booster: WPBB Box 25, Booster Color: Blue, Conductor Type: Run: ACSR,
AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.364 - 0.568
IN, Cable Diameter Range (tap): 0.386 - 0.572 IN, Conductor Size (run -
Mm): 9 - 14 SQ-MM

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872956
UPC 12 Digit	7818108729566

Dimensions

Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in

Conductor Related

Conductor - ACSR Str Run	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	2/0 AWG-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)