



WCB28

by Burndy
Catalog ID: WCB28

Prop 65 Notice

Wejtap connector installed with blue booster, .532-.650 (Run), .525-.650 (Tap).

Features: With Blue Power Booster, ANSI Class AA, Booster Color: Blue, Color Code: Blue, Conductor Size (tap - Mm): 13 - 17 SQ-MM, Installation Tool: WTRB Tool, Booster: WPBB Box 25, Cable Diameter Range (run): 0.532 - 0.65 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (tap): 0.525 - 0.65 IN, Conductor Size (run - Mm): 14 - 17 SQ-MM

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873359
UPC 12 Digit	7818108733599

Dimensions

Dimension - F Width Center to Center inch	1.89 in
Dimension - G inch	1.05 in

Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil
Conductor - ACSR Str Tap Range	4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Run Range	250 kcmil-300 kcmil
Conductor - AL Str Tap	4/0 AWG;250 kcmil;266 kcmil;300 kcmil
Conductor - AL Str Tap Range	4/0 AWG-300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)