



WCB43

by Burndy
Catalog ID: WCB43

Prop 65 Notice

Wejtap connector installed with blue booster, .600-.684 (Run), .324-.500 (Tap).

Features: With Blue Power Booster, ANSI Class AA, Color Code: Blue, Booster Color: Blue, Installation Tool: WTRB Tool, Booster: WPBB Box 25, Conductor Size (tap - Mm): 8 - 13 SQ-MM, Cable Diameter Range (run): 0.6 - 0.684 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Conductor Size (run - Mm): 15 - 17 SQ-MM, Cable Diameter Range (tap): 0.324 - 0.5 IN

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810873557
UPC 12 Digit	7818108735577

Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	1 (6/1) Robin AWG-1/0 (6/1) Raven AWG
Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Tap Range	1 AWG-3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)