



WCR31

by Burndy Catalog ID: WCR31

Prop 65 Notice

Wejtap connector installed with red booster, .257-398 (Run), .162-.258 (Tap).

Features: Without Red Power Booster, ANSI Class AA, Booster: WPBR Box 25, Conductor Size (tap - Mm): 4 - 7 SQ-MM, Installation Tool: WTRB Tool, Color Code: Red, Cable Diameter Range (run): 0.257 - 0.398 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Conductor Size (run - Mm): 7 - 10 SQ-MM, Cable Diameter Range (tap): 0.162 - 0.258 IN

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Color	Red
Connector Type	Тар
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Туре	Wejtap Connector
UPC	781810872109
UPC 12 Digit	7818108721099

Dimensions

Dimension - F Width Center to Center inch	1.40 in
Dimension - G inch	0.92 in

Conductor Related

Conductor - ACSR Str Run	4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - AL Str Run	2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG;3 AWG
Conductor - AL Str Tap Range	8 AWG-3 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No	
Standards - RoHS Compliance Status	СМ	
UL Listed	No	
Logistics		

Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)