



# WCR32

by Burndy  
Catalog ID: WCR32

Prop 65 Notice

Wejtap connector installed with red booster, .204-.326 (Run), .162-.258 (Tap).

Features: Without Red Power Booster, ANSI Class AA, Installation Tool: WTRB Tool, Color Code: Red, Conductor Size (tap - Mm): 4 - 7 SQ-MM, Booster: WPBR Box 25, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.204 - 0.326 IN, Cable Diameter Range (tap): 0.162 - 0.258 IN, Conductor Size (run - Mm): 5 - 8 SQ-MM

## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Sub Brand	WEJTAP
Type	Wejtap Connector
UPC	781810872154

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)