



WCR33

by Burndy
Catalog ID: WCR33

Prop 65 Notice

Wejtap connector installed with red booster, .169-.258 (Run), .162-.230 (Tap).

Features: Without Red Power Booster, ANSI Class AA, Color Code: Red, Installation Tool: WTRB Tool, Conductor Size (tap - Mm): 4 - 6 SQ-MM, Booster: WPBR Box 25, Cable Diameter Range (run): 0.169 - 0.258 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Conductor Size (run - Mm): 4 - 7 SQ-MM, Cable Diameter Range (tap): 0.162 - 0.23 IN

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Color	Red
Connector Type	Tap
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872208
UPC 12 Digit	7818108722088

Dimensions

Dimension - F Width Center to Center inch	1.40 in
Dimension - G inch	0.92 in

Conductor Related

Conductor - ACSR Str Run	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-5 (6/1) Thrush AWG
Conductor - AL Str Run	8 AWG;6 AWG;4 AWG
Conductor - AL Str Run Range	8 AWG-4 AWG
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG
Conductor - AL Str Tap Range	8 AWG-4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)