



WCY121

by Burndy
Catalog ID: WCY121

Aluminum Overhead Wedge Tap Connector, 1272 ACSR (Run), 1272 ACSR (Tap)

Product Details

General

Connector Type	Tap
Material	Aluminum
UPC	781810095768
UPC 12 Digit	7818100957688

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.00 in

Conductor Related

Conductor - ACSR Str Run	1113 (54/19) Finch;1272 (54/19) Pheasant;1431 (54/19) Plover
Conductor - ACSR Str Run Range	1113 (54/19) Finch-1431 (54/19) Plover
Conductor - ACSR Str Tap	1113 (54/19) Finch;1272 (54/19) Pheasant;1431 (54/19) Plover
Conductor - ACSR Str Tap Range	1113 (54/19) Finch-1431 (54/19) Plover
Conductor - AL Str Run	1272.2;1300;1351.5;1400;1431;1500;1590;1600
Conductor - AL Str Run Range	1272.2-1600
Conductor - AL Str Tap	1300;1351.5;1400;1431;1500;1590;1600
Conductor - AL Str Tap Range	1300-1600

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)