

# WCY56

by Burndy  
Catalog ID: WCY56

Prop 65 Notice

WEJTAP Assembly, 0.75-0.54(Run), 0.75-0.52(Tap).

Features: With Yellow Power Booster, ANSI Class AA, Installation Tool: WTRB, WTY Tool, Booster: WPBY Box 25, Booster Color: Yellow, Conductor Size (tap - Mm): 13 - 19 SQ-MM, Color Code: Yellow, Cable Diameter Range (run): 0.537 - 0.75 IN, Conductor Type: Run: AAC, Tap: AAC, Copper, Conductor Size (run - Mm): 14 - 19 SQ-MM, Cable Diameter Range (tap): 0.524 - 0.75 IN



## Product Details

### General

|                |   |
|----------------|---|
| Application    | For use in tap applications using large run and tap conductor sizes |
| Connector Type | Tap   |
| Material       | Copper  |
| Sub Brand      | WEJTAP  |
| Trade Name     | WEJTAP™   |
| Type           | Wejtap Connector  |
| UPC            | 781810874202  |
| UPC 12 Digit   | 7818108742022   |

### Dimensions

|   |         |
|---|---------|
| Dimension - F Width Center to Center inch | 3 in    |
| Dimension - G inch                        | 1.37 in |

### Conductor Related

|                                |  |
|--------------------------------|--|
| Conductor - ACSR Str Run       | 4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil |
| Conductor - ACSR Str Run Range | 4/0 (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil  |
| Conductor - ACSR Str Tap       | 4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil                         |
| Conductor - ACSR Str Tap Range | 4/0 (6/1) Penguin AWG-397.5 (24/7) Brant kcmil   |
| Conductor - AL Str Run         | 4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil  |
| Conductor - AL Str Run Range   | 4/0 AWG-450 kcmil  |
| Conductor - AL Str Tap         | 4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil  |

|                              |  |
|------------------------------|--|
| Conductor - AL Str Tap Range | 4/0 AWG-450 kcmil  |
| Conductor Type               | <ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul> |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)