

WCY57

by Burndy
Catalog ID: WCY57

Prop 65 Notice

Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.190 (Max), .979 (Min).

Features: With Yellow Power Booster, ANSI Class AA, Conductor Size (tap - Mm): 7 - 8 SQ-MM, Installation Tool: WTRB Tool, Color Code: Yellow, Booster Color: Yellow, Booster: WPBY Box 25, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.666 - 0.893 IN, Conductor Size (run - Mm): 17 - 23 SQ-MM, Cable Diameter Range (tap): 0.257 - 0.326 IN



Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810874257
UPC 12 Digit	7818108742577

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich-556.5 (24/7) Parakeet
Conductor - ACSR Str Tap	4 (7/1) Swanate;3 (6/1) Swallow;2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin
Conductor - ACSR Str Tap Range	4 (7/1) Swanate-1 (6/1) Robin
Conductor - AL Str Run	336.4;350;397.5;400;450;477;500;550;556.5;600
Conductor - AL Str Run Range	336.4-600
Conductor - AL Str Tap	4;3;2;1
Conductor - AL Str Tap Range	4-1
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)