



WCY79

by Burndy
Catalog ID: WCY79

Prop 65 Notice

Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.670 (Max), 1.526 (Min).

Features: With Yellow Power Booster, ANSI Class AA, Conductor Size (tap - Mm): 9 - 18 SQ-MM, Booster Color: Yellow, Color Code: Yellow, Installation Tool: WTRB Tool, Booster: WPBY Box 25, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.889 - 1.133 IN, Conductor Size (run - Mm): 23 - 29 SQ-MM, Cable Diameter Range (tap): 0.364 - 0.722 IN

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Sub Brand	WEJTAP
Type	Wejtap Connector
UPC	781810875353

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)