



WSL7

by Burndy
Catalog ID: WSL7

Prop 65 Notice

Stirrup Assembly, Large stirrups,Run:.927-.846,Tap:.324-.324.

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Color Code: Yellow, Installation Tool: WTRBYK Tool, Booster: WPBY Box 25, Cable Diameter Range (run): 0.846 - 0.927 IN, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Cable Diameter Range (tap): 0.324 - 0.324 IN, Bail Size: 1/0 AWG

Product Details

General

Application	For Common ACSR, Aluminum And Copper Conductors
Sub Brand	WEJTAP, STIRRUP
Type	Wejtap with Stirrup
UPC	781810877401

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)