



## WSM3

by Burndy  
Catalog ID: WSM3

Prop 65 Notice

Stirrup assembly, 3/0, 4/0 AWG, Bail size: 2.

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Color Code: Blue, Booster: WPBB Box 25, Installation Tool: WTRBYK Tool, Cable Diameter Range (run): 0.41 - 0.563 IN, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Bail Size: 2 AWG, Cable Diameter Range (tap): 0.25 - 0.25 IN

## Product Details

### General

Application	For Common ACSR, Aluminum And Copper Conductors
Material	Aluminum
Physical Attribute - Number of Holes	1
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup
UPC	781810876855
UPC 12 Digit	7818108768555

### Dimensions

Dimension - Bail Size	2
Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in

### Conductor Related

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Size	3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)