



WSM4

by Burndy
Catalog ID: WSM4

Prop 65 Notice

Stirrup assembly, 3/0, 4/0 AWG, Bail size: 2/0.

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Booster: WPBB Box 25, Color Code: Blue, Installation Tool: WTRBYK Tool, Cable Diameter Range (run): 0.41 - 0.563 IN, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Bail Size: 2 AWG, Cable Diameter Range (tap): 0.375 - 0.375 IN

Product Details

General

Application	For Common ACSR, Aluminum And Copper Conductors
Material	Aluminum
Physical Attribute - Number of Holes	1
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup
UPC	781810876909
UPC 12 Digit	7818108769099

Dimensions

Dimension - Bail Size	2/0
Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.4 in

Conductor Related

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Size	3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Size	3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)