



## Y10AC9

by Burndy  
Catalog ID: Y10AC9

Prop 65 Notice

Electric Hydraulic Pump, 10000 psi, Weight 28 lbs.

- Easy to carry and transport
- Factory set relief valve
- 100,000+ life cycles
- Sealed electric pendant switch with 10-foot cord

Features: The Y10AC9 Electric Hydraulic Pump Is For Use With All HYPRESS Heads And Cutters Requiring 10,000 PSI Operating Pressure, Lightweight, Small Size: Easy To Lift, Carry And Transport Tool Around Job Site With Lightweight Body And Handle, Factory Set Relief Valve: High Quality Crimps Are Achieved With Built-In, Factory Set Pressure Relief Valve And Audible Recycling Of Pump To Signal Completion Of Crimp Cycle, 100,000 (+) Life Cycles: Long Durable Life Expectancy With Lightweight Cast Aluminum Reservoir Body, Convenient 115V AC Electric Powered Motor, Saves Time With Quick Disconnect Hydraulic Fitting, Sealed Electric Pendant Switch: Easy Operation With Durable Remote Pendant Switch With 10-Foot Cord, 5-Year Limited Warranty, The Y10AC9 Electric Hydraulic Pump Is For Use With All HYPRESS Heads And Cutters Requiring 10000 PSI Operating Pressure, The Y10AC9 Is Equipped With A Built-In, Factory Set Pressure Relief Valve, An Audible Pop And Recycling Of The Pump As Well As Relaxing Of The Hose Signal Completion Of The Crimping/Cutting Cycle, Pump Is Supplied With A Durable Hand-Held Electric Pendant Switch, Current Draw (maximum): 11 AMP, Base: 6.5 X 8.25 IN, Reservoir Volume: 1.6 QT, Weight: 28 LB, Accessories: YAC-CASE Steel Carrying Case With Handle And Locking Latch, Replacement Fluid: Alfluid5 year limited warranty

## Product Details

### General

Application	For Y34BH, Y35BH, Y35BH4, Y39BH, Y45, Y46, Y46C, Y750BHXT, Y750CBHXT, Y644MBH, Y4PC834MBH, Y81KFTMBH, Y60BHU, RHCC129ACSR, RHCC245CUAL
Power Source	115 V AC 5/8 HP Motor, 10000 R.P.M.
Sub Brand	HYPRESS
Tool Type	Electric Hydraulic Pump
Type	Pumps
UPC	781810467299
UPC 12 Digit	7818104672999

### Dimensions

Height	14.38 in
Length	8.25 in
Weight	28 lb
Width	6.50 in

### Electrical Ratings

Current Draw Max	11A
------------------	-----

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)