



Y10D

by Burndy
Catalog ID: Y10D

Hand Held Plier Type Tool, 22 AWG-10 AWG Bare and Nylon Insulated.

Easy wire cutting with precision machined cutting blade, Easy tool operation out of the carton. No need to break in the tool prior to actual usage, Comfort grip handles fit hands comfortably helping make the tool easy to use

Product Details

General

Application	Crimping
Sub Brand	HYTOOL
Tool Type	Hand-held plier tool
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810700860

Conductor Related

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)