

BUR_SKU-Y122CMR

Y122CMR

by Burndy
Catalog ID: Y122CMR

Prop 65 Notice

High Strength Steel Ergonomic Ratchet Hand Tool, 1.3 lb Weight.

- Overmolded comfort grip handles
- Easy groove identification with color coded dies
- UL Listed/CSA Certified connections when used with recommended BURNDY terminals/splices
- Die index embossment for all 6 wire ranges
- Emergency release mechanism in case of misalignment or mistaken die choice
- Two different kits are also available with a selection of connectors in a sturdy metal carrying case (Y122CMRKIT and Y122CMRCIKIT)

Ratchet Compression Tool, Long Handles And Overmolded Grips Provide Low Handle Force And Increase Ergonomics5 year limited warranty

Product Details

General

Application	Crimping
Die Type	Rotating Die Wheel
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimp Tool
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810659694
UPC 12 Digit	7818106596944

Dimensions

Height	1.00 in
Length	10.38 in
Weight	1.3 lb
Width	3.00 in

Conductor Related

Crimping Ranges	Copper: #12 AWG - #2 AWG Stranded, Solid and Flex
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)