

## Y1MRTCKIT

by Burndy  
Catalog ID: Y1MRTCKIT

Prop 65 Notice

Full Cycle Ratchet Tool with Connectors in a Metal Carrying Case.

- Heavy gauge steel cover / body
- Rugged clasp and handle provide long carry case life
- Individual compartments hold a variety of connectors, cover prohibits spillage of connector contents when closed
- Foam insert contains Y1MR HYTOOL™ and helps to protect tool from impact if case is dropped
- Kit identification label outlines kit contents and provides connector installation information

Includes: Y1MRTC Full-Cycle Ratchet Tool, Sturdy Metal Carrying Case, Terminals: YA8CL2TC14, YA8CL2TC14, YA6CL2TC14E1, YA6CL2TC38, YAV6CL2TC14FX, YA4CL2TC38, YA2C2TC38, YA2CL2TC14, YA8CL2TC38, YA6CL2TC14, YA6CL2TC14E2, YAV6CL2TC14E2FX, YA4CL2TC14, YA3C2TC38, YA2CL2TC38, Thin-Wall C-Taps: YC4L125 year limited warranty on Tool



## Product Details

### General

Application	Type Y1MRTC mechanical full cycle ratchet HYTOOL will accommodate copper compression hydენტconnectors for #8 through #1 code conductor, #8 through #2 Class I flexible strand copper conductor, and #2 solid.
Sub Brand	HYTOOL
Tool Type	Tool Kit
Type	Crimpers
UPC	781810276761
UPC 12 Digit	7818102767611

### Dimensions

Height	2.06 in
Length	17.85 in
Width	7.38 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)