



Y352

by Burndy
Catalog ID: Y352

Prop 65 Notice

Self Contained Hydraulic Hand Operated Crimping Tool, 12 Ton, 10000 psi, 8 AWG - 750 kcmil Copper, 8 AWG - 750 kcmil Aluminum, 3/16" Rubber Covering.

- Comfort grip handles
- Trigger controlled ram release
- Short handle throw
- Rubber covered handles
- 180° head rotation
- C-shaped head
- Hole for lifting eye
- Positive push button die locks
- Rubber body covering
- Built-in automatic 10,000 psi "Blow-Off" pressure release valve
- Rapid ram advance handle
- Y35-2 has rubber covered head

Compact C shaped head allows easy placement and removal from continuous conductor lengths, Easy to position tool for work with 180° head rotation, Easy die change accomplished with push button die locks, Body and handles covered with 3/16 molded rubber for tool impact protection 5 year limited warranty

Product Details

General

Application	For Use On: Copper 8 AWG Stranded - 500 KCMIL Code Cables Grounding Terminals and splices, Copper: 8 AWG Stranded - KCMIL And Upto 3/4 IN Ground Rod , Copper 8 AWG Stranded - 750 KCMIL Code Cables, N30-N500 Navy Cables, Flexible and Extra Flex insulated and uninsulated terminals, Upto 400 KCMIL Splices, Aluminum 8 AWG Stranded - 750 KCMIL Code Cables Pin Terminals, Upto 350 KCMIL Splices - refer to catalog for specific connectors
Crimp Force Capacity	12 ton
Die Type	U DIE
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810408445
UPC 12 Digit	7818104084455

Dimensions

Height	2.75 in
Length	23.25 in
Weight	13.5 lb
Width	4.75 in

Conductor Related

Crimping Ranges

Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only; Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)