



Y35

by Burndy Catalog ID: Y35

Prop 65 Notice

Self Contained Hydraulic Crimping Tool, 12 Ton Output Force, 10000 psi, 8 AWG-750 kcmil, 8 AWG-750 kcmil Aluminium, Up to $3/4^{\prime\prime}$ Ground Rod, U Dies.

- Comfort grip handles
- Trigger controlled ram release
- Short handle throw
- Rubber covered handles
- 180° head rotation
- C-shaped head
- Hole for lifting eye
- Positive push button die locks
- Rubber body covering
- Built-in automatic 10,000 psi "Blow-Off" pressure release valve
- Rapid ram advance handle
- Y35-2 has rubber covered head

Compact C shaped head allows easy placement and removal from continuous conductor lengths, Easy to position tool for work with 180° head rotation, Body and handles covered with 3/16 molded rubber for tool impact protection, Easy die change accomplished with push button die locks5 year limited warranty

Product Details

General

Application	Crimping
Crimp Force Capacity	12 ton
Die Type	U DIE
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Туре	Crimpers
UPC	781810408407
UPC 12 Digit	7818104084077

Dimensions

Height	2.75 in
Length	23.25 in
Weight	13.5 lb
Width	4.75 in

Conductor Related

Crimping Ranges	Copper: #8 str 500 kcmil code cable; Copper: #8 str 500 kcmil and up to 3/4" ground rod; Copper: #8 str 750 kcmil code cable, N30 - N500
	Navy cable, flexible, and extra flex; Splices to 400 kcmil only; Aluminum: #8 str 750 kcmil code cable

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)