

## Y3634R

by Burndy  
Catalog ID: Y3634R

Prop 65 Notice

Cu Comp Reducer Adapter Sleeve Code Cond, 600-500 kcmil, 600 V-35 kV, 2.69 " L, Tin Plated, For Cu.

Wide range of conductors are accommodated, Length fits the long barrel connector design (YS, YA), Can be used on all long barrel connectors. Field cut to fit shorter length compression barrels (YS-L, YA-L), Manufactured from high conductivity electrolyti



## Product Details

### General

Application	Reducer
Connector Type	Reducer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	REDUCER/ADAPTER
Temperature Rating	194
Type	Y-R, Compression
UPC	781810036822
UPC 12 Digit	7818100368222

### Dimensions

Dimension - B Length inch	2.69 in
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.69 in
Dimension - Outside Diameter inch	0.910 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Run	600 kcmil
Conductor - Copper Str Run Range	600 kcmil
Conductor - Copper Str Tap	500 kcmil
Conductor - Copper Str Tap Range	500 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)