



Y39

by Burndy
Catalog ID: Y39

Prop 65 Notice

Remote Operated Hydraulic Crimping Tool, 12 Ton, 10000 psi, 8 AWG - 750 kcmil Copper, 6 AWG - 750 kcmil Aluminum, 14 AWG-556.5 kcmil ACSR.

- Leather die retainer strap
- 180° head rotation
- Rubber body cover
- Built in automatic 10,000 psi audible pop-off pressure release valve
- Rapid ram advance handle
- Short handle stroke
- Recessed die retainer spring latch
- Positive push button die locks
- Rubber covered handles
- Trigger controlled ram release
- Comfort grip handles

Remote Operated Hydraulic Crimping Tool, 12 Ton, 10000 psi, 8 AWG - 750 kcmil Copper, 6 AWG - 750 kcmil Aluminum, 14 AWG-556.5 kcmil ACSR 5 year limited warranty

Product Details

General

Application	For Use On: Copper Cable: 6 AWG - 750 KCMIL Stranded Code Cable, N30 - N650 Navy Cable Flexible And Extra Flexible Terminals and splices, Copper-AN or AIR: 6 - 4/0 AWG Stranded Code Cable, AN6 - AN 4/0 AWG Aircraft Cable, Copper: 8 - 2/0 AWG Stranded Code Cable, AN8 - AN 2/0 AWG Aircraft Cable, Copper: 12 AWG Solid - 250 KCMIL, Aluminum: 8 AWG - 750 KCMIL Stranded Code Cable (YA-A Terminals, YS-A, YS-AT, YRB Splices), Aluminum: 6 AWG - 500 KCMIL Stranded (YFD, YFN, YFO Taps)
Crimp Force Capacity	12 ton
Die Type	U DIE
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810625002
UPC 12 Digit	7818106250022

Dimensions

Height	8.75 in
Length	23.00 in
Weight	12 lb
Width	4.00 in

Conductor Related

Crimping Ranges	Copper #6 AWG - 750 kcmil str. Code Cable N30 - N650 Navy Cable, Flexible, and Extra Flexible; Copper AN or AIR #6 AWG - 4/0 str. Code Cable AN6 - AN4/0 Aircraft Cable, Flexible, and Extra Flexible; Copper #8 AWG - 2/0 str. Code Cable AN8 - AN2/0 Aircraft Cable, Flexible, and Extra Flexible; Copper #12 AWG sol. - 250 kcmil; Aluminum #8 AWG - 750 kcmil Code Cable; Aluminum #6 str. - 500 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)