



Y500CTHS

by Burndy
Catalog ID: Y500CTHS

Prop 65 Notice

Hydraulic Crimp Tool, 17.6 in L, 6 tons.

- Permanent functional D3 groove (no die needed)
- Used with W, X, and W-VT style dies
- 180° head rotation
- Enhanced clearance for tap connectors

Die Accommodation: W, X Dies5 year limited warranty

Product Details

General

Application	For Use On: Copper, Aluminum, ASCR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed, Compact, Stranded & Solid conductors, Installs splices, taps, or terminations: 8 AWG - 500 KCMIL Stranded Copper, 8 AWG - 350 KCMIL Flex, 8 AWG - 350 KCMIL Aluminum
Crimp Force Capacity	6 ton
Die Type	W and X styles
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810270387
UPC 12 Digit	7818102703877

Dimensions

Height	2.68 in
Length	18 in
Weight	7.8 lb
Width	5.5 in

Conductor Related

Crimping Ranges	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed, Compact, Stranded and Solid conductors, Installs Splices, Taps or Terminations: #8 - 600 kcmil Copper Str., #8 - 350 kcmil Flex, #8 - 350 kcmil Aluminum
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)