



Y644HSXT

by Burndy
Catalog ID: Y644HSXT

Prop 65 Notice

Dieless Hypress, #6 - 1000 kcmil Cu #6 - 750 kcmil Al, 11 Tons, Hydraulic Hand Operated Tool.

- Ergonomic handle design
- Comfort grip handles
- Handle trigger drain
- 355° head rotation
- Dieless system
- Audible "Pop-Off" pressure relief valve
- Pivoting die nest

Features: Ergonomic handle design, Comfort grip handles, Handle trigger drain, 355DEG C head rotation, Dieless system, Audible Pop-Off pressure relief valve, Pivoting die nest5 year limited warranty

Product Details

General

Application	For Use On Conductor: Copper Cable: 6 - 1000 KCMIL , Aluminum Cable: 6 - 750 KCMIL, For Use On Terminals: YA-L, YA-2LN, YA, YA-FXB, YA-2N, YA-L-2TC, YA-L-FX, YAB-4N, YA-L-TC, YA-2L, YA-4N, YEV-P-FX, YE-P, YE-P-FX, YA-A, YA-A-TN, For Use On Splices: YS-L, YS, YS-T, YS-A, For Use On Pin Adapter: HYPLUG AYP, AYPO
Crimp Force Capacity	11 ton
Die Type	Dieless
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810458358
UPC 12 Digit	7818104583588

Dimensions

Height	3.00 in
Length	23.20 in
Weight	15 lb
Width	7.04 in

Conductor Related

Crimping Ranges	Copper #6 - 1000 kcmil, Aluminum #6 - 750 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)