



Y750HSXT

by Burndy
Catalog ID: Y750HSXT

Prop 65 Notice

Self Contained Hydraulic Hand Operated Crimping Tool, 12 Ton, 14 AWG - 750 kcmil Copper, 8 AWG - 750 kcmil Aluminium, 4 AWG - 556.5 kcmil ACSR.

- Easy tool positioning with its 355° head rotation
- Patented rapid advance pump for faster crimps
- Comfort grip handles
- Audible "pop-off" pressure relief valve
- Handle drain trigger

Easy tool positioning with its 355° head rotation, Patented rapid advance pump for faster crimps, Handle trigger drain for convenient ram retraction 5 year limited warranty

Product Details

General

Application	Crimping
Crimp Force Capacity	12 ton
Die Type	U DIE
Sub Brand	HYPRESS
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810458600
UPC 12 Digit	7818104586000

Dimensions

Height	2.90 in
Jaw Width	1.70 in
Length	23.96 in
Weight	17.2 lb
Width	8.71 in

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)