



Y81KFT

by Burndy
Catalog ID: Y81KFT

Prop 65 Notice

Dieless Hypress, #8 - 1000 kcmil Cu #8 - 750 kcmil Al, 6 tons, Hydraulic Hand Operated.

- Dieless Design
- UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: Straight

Product Details

General

Application	Crimping
Crimp Force Capacity	6 ton
Die Type	Dieless
Sub Brand	4-POINT
Tool Type	Self-Contained Hydraulic Crimper
Trade Name	4-POINT®
Type	Crimpers
UPC	781810376997
UPC 12 Digit	7818103769977

Dimensions

Height	7.7 in
Length	25.6 in
Weight	12 lb
Width	2.5 in

Conductor Related

Crimping Ranges	Copper: #8 AWG - 1000 kcmil; Copper Flex: #8 - 777.7 kcmil; Aluminum: #8 - 750 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)