

Y8MRB1

by Burndy
Catalog ID: Y8MRB1

Hand Held Full Cycle Ratchet Crimping Tool, 22 -8 AWG.

- Light weight
- Each indenter has unique identifying marks for inspectability
- Fully enclosed, protected ratchet mechanism does not allow the handles to be opened until full ratchet cycle is completed
- Inspection gauges available to check each groove

Features: One Tool To Accomodate #22-8 AWG, Lightweight, Full Cycle Ratchet For Positive Crimping, Inspection (PG) Gauges Available To Check Each Groove, Each Indenter Has Its Own Identifying Mark For Inspectability, Jaw Opening Orientation, Molded Finger And Palm Grips And The Easy Reach Frame Minimize User Fatigue, Dieless: No, Handle Length: 9-1/2 IN, Weight: 1.21 LB, Wire Stripper: No, Crimps Coaxial Connectors: No, Wire Cutter: No 5 year limited warranty



Product Details

General

Application	For 8-22 AWG Uninsulated Terminals And Splices
Die Type	Permanent Dies
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimp Tool
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810031100
UPC 12 Digit	7818100311000

Dimensions

Height	1.04 in
Length	10.56 in
Weight	1.21 lb
Width	3.50 in

Conductor Related

Crimping Ranges	#22 - #8 AWG
-----------------	--------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)