



YA252NTC38

by Burndy
Catalog ID: YA252NTC38

Prop 65 Notice

Cu Tubing Hylug, 2 Holes w/o Inspection Window, 1/0 AWG Code, 100 Navy, 600V-35kV, 3/8" stud, Long, Compression, 0.40 in BCD, Pink.

Features: Compression Terminal, Die Index: 12 or 348, Strip Length: 1-7/16 IN, Tongue Angle: Straight, Finish: Tin Plated

Product Details

General

Application	For Use On: UL Listed 90 DEG C, 600 Volts to 35 kV
Color Code	Pink
Connector Type	Terminal
Die Index	12
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810020357
UPC 12 Digit	7818100203577

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.37 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	3/8

Dimension - Thread Size	3/8
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Solid Size Range	1/0 AWG
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Size	1/0
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)