

YA28L2TC38

by Burndy
Catalog ID: YA28L2TC38

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 4/0 AWG, 3/8" Stud, 1" Stud Hole Spacing, Short Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Die Index: 15, Tongue Angle: Straight, Wire Strip Length: 1-1/8 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W28VT, W28RT Die, (2), X28RT Die, (3), Hydraulic: BCT500HS, Y500CTHS Tool, W28VT, W28RT Die, (2), X28RT Die, (3), Y35, Y39, Y750, PAT750 Tool, U28RT Die, (1), Y46 Tool, U28RT Die With PUADP-1 Adapter, (1), Color Code: Purple, Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11 Tool, (1), MRC840 Tool, (2), Conductor Type: Commercial Stranded Copper



Product Details

General

| | |
|--------------------------------------|---------------------------------------------------------------------------------|
| Application | For Code Conductor |
| Color Code | Purple |
| Connector Type | Terminal |
| Die Index | 15 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810503669 |
| UPC 12 Digit | 7818105036699 |

Dimensions

| | |
|---------------------------------|---------|
| Bolt Size | 3/8 in |
| Dimension - B Length fraction | 7/8 in |
| Dimension - B Length inch | 0.88 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 in |
| Dimension - Hole Size mm | 10 mm |

| | |
|-----------------------------------|----------|
| Dimension - L Length Overall mm | 82 mm |
| Dimension - Length Overall inch | 3.22 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 0.69 in |
| Dimension - Pad Width inch | 1.02 in |
| Dimension - Strip Length inch | 1-1/8 |
| Dimension - Stud Size inch | 3/8 |
| Dimension - Thread Size | 3/8 |
| Dimension - Z inch | 0.41 in |
| Length | 3.22 in |
| Outside Diameter | 0.69 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|---------------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Navy Size | 200 (61) Navy |
| Conductor - Copper Str Size | 4/0 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)