

## YA2C

by Burndy  
Catalog ID: YA2C

Prop 65 Notice

Copper Compression Lug, 1 Hole w/o Inspection Window, 2 AWG, 5/16" Stud, Long Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 1-5/16 IN, Temperature Rating: 90 DEG C, Die Index: 10, Color Code: Brown, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (2), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (2), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (2), Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, MY29-3, MY29-11, MRC840 Tool, (2), Y1MRTC Tool, (4), Conductor Type: Commercial Stranded Copper



## Product Details

### General

Application	For Code Conductor
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810500651
UPC 12 Digit	7818105006511

### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.59 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.29 in

Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)