



YA30A3

by Burndy Catalog ID: YA30A3

Prop 65 Notice

Aluminum Compression Lug, 2 Hole w/o Inspection Window, 300 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Tin Plated.

UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: Straight

Product Details

General

Application	For Aluminum & Copper Conductors		
Color Code	Blue		
Connector Type	Terminal		
Die Index	470		
Feature - Barrel Style	Chamfered		
Feature - Barrel Type	Standard		
Material	Aluminum		
Physical Attribute - Number of Holes	2		
Physical Attribute - Tongue Type	Standard		
Plated	Y		
Plating Type	Tin - Electro Plated		
Sub Brand	TERMINALS, HYLUG		
Temperature Rating	194		
Trade Name	HYLUG™		
Туре	YA-A		
UPC	781810755402		
UPC 12 Digit	7818107554022		

Dimensions

Dimension - B Length fraction	1-9/16 in
Dimension - B Length inch	1.53 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.11 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.64 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Pad Width inch	1.38 in

Dimension - Strip Length inch	1-3/4
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.73 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	300 kcmil	
Conductor - AL Str Size Range	300 kcmil	
Conductor - Copper Str Size	300 kcmil	
Conductor - Copper Str Size Range	300 kcmil	

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Minimum Pack Quantity		

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)