



# **YA30A5**

by Burndy Catalog ID: YA30A5

Prop 65 Notice

UNINSULATED ALUMINUM COMPRESSION TERMINAL, 1-HOLE DESIGNUL Listed 90° C600 Volts to 35 KV.

## **Product Details**

#### General

Color Code	Blue
Connector Type	Terminal
Die Index	470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810023501
UPC 12 Digit	7818100235011

## Dimensions

Dimension - B Length fraction	1-9/16 in
Dimension - B Length inch	1.53 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.89 in
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	112 mm
Dimension - Length Overall inch	4.42 in
Dimension - N inch	0.44 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Pad Width inch	1.38 in
Dimension - Strip Length inch	1-3/4
Dimension - Stud Size inch	3/8
Dimension - Thread Size	3/8

Dimension - Z inch	0.45 in
Physical Attribute - Tongue Angle	Straight

## **Electrical Ratings**

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - AL Str Size	300 kcmil
Conductor - AL Str Size Range	300 kcmil
Conductor - Copper Str Size	300 kcmil
Conductor - Copper Str Size Range	300 kcmil

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

## Logistics

nimum Pac	k Quantity	15	
-----------	------------	----	--

## For further technical assistance, please contact us

## **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

## **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)