



YA30LTC516FX

by Burndy
Catalog ID: YA30LTC516FX

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 250 Flex, 5/16" Stud, Short Barrel, Tin Plated

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810138618
UPC 12 Digit	7818101386188

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.31 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1-1/16 in
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	250 kcmil
Conductor - Copper Flex H Size	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)