



YA32LNT12

by Burndy
Catalog ID: YA32LNT12

1 Hole HYLUG Uninsulated Cu Compression Terminal, Narrow Tongue,
400 kcmil, 600 V - 35 KV, 1/2" stud, Standard Barri, Blue

Product Details

General	
Color Code	Blue
Connector Type	Terminal
Die Index	19
Feature - Barrel Style	• Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810270745

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.20 in
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.21 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	400 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)