



YA32LTC38FX

by Burndy
Catalog ID: YA32LTC38FX

Prop 65 Notice

Cu Comp Terminal Flex Cond, Bvl Entry, 1 Hole/W/InspWindow, 313.1 kcmil(775/#24)DLO, 300 kcmil Flex, 600 V-35 kV, 3/8" Stud, Std bbl, Red, 18 or 324 Index.

UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available,Tongue Angle: Straight

Product Details

General

Application	For Flex Conductor
Color Code	Red
Connector Type	Terminal
Die Index	18;324
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810144077
UPC 12 Digit	7818101440777

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.68 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	1-1/4

Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	313.1 (775/#24) DLO
Conductor - Copper DLO Size Range	313.1 (775/#24) DLO
Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex G Size Range	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex H Size Range	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex I Size Range	300 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex K Size Range	300 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Flex M Size Range	300 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)