

YA32

by Burndy
Catalog ID: YA32

Prop 65 Notice

Copper Compression Lug, 1 Hole w/o Inspection Window, 400 kcmil, 5/8" Stud, Long Barrel, Electro Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 2-3/16 IN, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Finish: Electro-Tin Plated, Die Index: 19 Or 470, Color Code: Blue, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W32VT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W32VT, W32RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U32RT, U30ART Die, (4), Y46 Tool, U32RT, U30ART Die With PUADP-1 Adapter, (4), Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (3), Conductor Type: Commercial Stranded Copper



Product Details

General

| | |
|--------------------------------------|-------------------------|
| Application | For Code Conductor |
| Color Code | Blue |
| Connector Type | Terminal |
| Die Index | 19;470 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Tin Plated |
| UPC | 781810505403 |
| UPC 12 Digit | 7818105054033 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length fraction | 2-1/8 in |
| Dimension - B Length inch | 2.12 in |
| Dimension - Bolt Hole Size inch | 0.69 in |
| Dimension - Bolt Size fraction | 5/8 |
| Dimension - Hole Size inch | 0.69 in |
| Dimension - Hole Size mm | 17 mm |
| Dimension - L Length Overall mm | 105 mm |
| Dimension - Length Overall inch | 4.15 in |

| | |
|-----------------------------------|----------|
| Dimension - N inch | 0.66 in |
| Dimension - Outside Diameter inch | 0.95 in |
| Dimension - Pad Width inch | 1.40 in |
| Dimension - Strip Length inch | 2-3/16 |
| Dimension - Stud Size inch | 5/8 |
| Dimension - Z inch | 0.67 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|----------------------------------|----------------|
| Conductor - Copper Str Navy Size | 400 (127) Navy |
| Conductor - Copper Str Size | 400 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)