



YA342N90

by Burndy
Catalog ID: YA342N90

Prop 65 Notice

Copper Two Hole HYLUG - Long Barrel ,90 Degree Pad 500 kcmil,1/2" Bolt Hole with 1-3/4" Spacing,Tin Plated,Color: Brown,Die Index : 20.

Features: Compression Terminal, Die Index: 20 or 299, Strip Length: 2-5/16 IN, Tongue Angle: 90 DEG

Product Details

General

Application	For Use On: UL Listed 90 DEG C, 600 Volts to 35kV
Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810080177
UPC 12 Digit	7818100801777

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	3.45 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.73 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	2-5/16
Dimension - Z inch	0.64 in

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)