

# YA34A12

by Burndy  
Catalog ID: YA34A12

Prop 65 Notice

Aluminum Stackable Terminal- Straight Lug, 500 Kcmil, Pink,1 hole,Tin - Electro Plated



## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	300
Feature - Barrel Style	Chamfered
Material	Aluminum
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810130711
UPC 12 Digit	7818101307111

### Dimensions

Dimension - B Length inch	2.34 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	188 mm
Dimension - Length Overall inch	7.42 in
Dimension - Outside Diameter inch	1.32 in
Dimension - P inch	3.65 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-5/8
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)