

YA34A8N131T38E

by Burndy
Catalog ID: YA34A8N131T38E

Prop 65 Notice

Cu & Al Compression terminal, 1 Hole/W/insp W, 4/0 AWG-500kcmil, 600V-35Kv, 3/8" stud, Pink, 300 Index , Narrow tongue terminal.

UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: Straight



* Representative image

Product Details

General

Application	YA-E Equipment terminals are designed to provide replacements for original equipment mechanical or other compression terminals
Sub Brand	TERMINALS, HYLUG
Type	YA-E
UPC	781810290286

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)