



YA362NFXB

by Burndy
Catalog ID: YA362NFXB

Prop 65 Notice

Cu Comp Terminal Flex Cond(Telecom), 2 Hole/W/O/InspWindow, 444.4 kcmil(1100/#24)DLO, 600 V-35 kV, 1/2" Stud, 1.75" Spacing, Lng bbl, Belled End.

Die Index: 20, Conductor Type: Flexible Copper, Wire Strip Length: 3-1/16 IN, Tongue Angle: Straight

Product Details

General

Application	For Flex Conductor
Color Code	Brown
Connector Type	Terminal
Die Index	20
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810039946
UPC 12 Digit	7818100399466

Dimensions

Dimension - B Length fraction	2-15/16 in
Dimension - B Length inch	2.95 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	174 mm
Dimension - Length Overall inch	6.84 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.18 in
Dimension - Pad Width inch	1.73 in
Dimension - Strip Length inch	3-1/16

Dimension - Stud Size inch	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444.4 (1100/#24)
Conductor - Copper DLO Size Range	444.4 (1100/#24)
Conductor - Copper Flex G Size	444.4
Conductor - Copper Flex G Size Range	444.4
Conductor - Copper Flex H Size	444.4
Conductor - Copper Flex H Size Range	444.4
Conductor - Copper Flex I Size	444.4
Conductor - Copper Flex I Size Range	444.4
Conductor - Copper Flex K Size	444.4
Conductor - Copper Flex K Size Range	444.4
Conductor - Copper Flex M Size	444.4
Conductor - Copper Flex M Size Range	444.4
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)