



YA382ENT38FX

by Burndy
Catalog ID: YA382ENT38FX

Prop 65 Notice

Cu conductor std barrel tubing, 2 holes W/O insp window, 535.3 kcmil.325/24(500 kcmil flex), 3/8" stud, Pink,L99 index

Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810426234

Dimensions

Dimension - B Length fraction	2-13/16 in
Dimension - B Length inch	2.81 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.03 in
Dimension - Inside Diameter inch	0.98 in
Dimension - L Length Overall mm	147 mm
Dimension - Length Overall inch	5.77 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.35 in
Dimension - Strip Length inch	3-1/16 in
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex G Size Range	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex H Size Range	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex I Size Range	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Copper Flex M Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)