



YA38LTC12FX90

by Burndy
Catalog ID: YA38LTC12FX90

Prop 65 Notice

Cu Tubing Hylug; 1 Hole with Inspection Window; 535.3 kcmil (1325/#24)
DLO, 500 Flex; 600V-35kV; 1/2" stud; Standard; Compression; 0.53 in
BCD; Pink

Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021453
UPC 12 Digit	7818100214533

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	2.80 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.90 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	0.55 in

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	535.3 (1325/#24) DLO
Conductor - Copper DLO Size Range	535.3 (1325/#24) DLO
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex G Size Range	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex H Size Range	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex I Size Range	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Copper Flex M Size Range	500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)