



YA39AM2

by Burndy Catalog ID: YA39AM2

Prop 65 Notice

Uninsul Al Comp Terminal, 2 Hole NEMA, 700-750 kcmil(Al/Cu), 900 kcmil Compt AL, 600 V-35 kV, 1/2" Stud, 1.75" Spacing, Closed bbl, Red, 301 Index.

UL Listed 90 DEG C, 600 V - 35 KV,Tongue Angle: Straight

Product Details

General

Application	For Aluminum & Copper Conductors		
Color Code	Red		
Connector Type	Terminal		
Die Index	301		
Feature - Barrel Style	Chamfered		
Feature - Barrel Type	Standard		
Material	Aluminum		
Physical Attribute - Number of Holes	2		
Physical Attribute - Tongue Type	Standard		
Plated	Y		
Plating Type	Tin - Electro Plated		
Sub Brand	TERMINALS, HYLUG		
Temperature Rating	194		
Trade Name	HYLUG™		
Туре	YA-A		
UPC	781810762004		
UPC 12 Digit	7818107620044		

Dimensions

Dimension - B Length fraction	2-9/16 in
Dimension - B Length inch	2.56 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.12 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	186 mm
Dimension - Length Overall inch	7.31 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.60 in
Dimension - Pad Width inch	1.69 in

Dimension - Strip Length inch	2 7/8
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.74 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil	
Conductor - AL Str Size Range	700 kcmil-750 kcmil	
Conductor - Copper Str Size	700 kcmil;750 kcmil	
Conductor - Copper Str Size Range	700 kcmil-750 kcmil	

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	Yes
Logistics	

1

	Minimum	Pack	Quantity	
--	---------	------	----------	--

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)