

YA41L

by Burndy
Catalog ID: YA41L

Copper Compression Lug, Single Hole w/ Inspection Window, 850 kcmil, 5/8" Stud, Short Barrel,26 index,Gold,Tin Plated



Product Details

General

Color Code	Gold
Connector Type	Terminal
Die Index	26
Feature - Barrel Style	• Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810367469

Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - D inch	1.33 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	105 mm
Dimension - Length Overall inch	4.15 in
Dimension - N inch	0.66 in

Dimension - Outside Diameter inch	1.38 in
Dimension - Pad Width inch	2.01 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size fraction	5/8
Dimension - Stud Size inch	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	850 kcmil
Conductor - Copper Str Size Range	850 kcmil
Conductor - Material	Copper

Certifications and Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)