



YA44L2NT38FX45

by Burndy
Catalog ID: YA44L2NT38FX45

Prop 65 Notice

Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, 777.7
kcmil(1925/#24)DLO, 750 kcmil FLEX, 600 V-35 kV, 3/8" Stud, 1.00"
Spacing, 45 Deg Bent, Std bbl.

UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: 45 DEG Angle

Product Details

General

Application	For Flex Conductor
Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin -Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810080429
UPC 12 Digit	7818100804299

Dimensions

Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8
Dimension - Height inch	3.07 in
Dimension - Hole Size inch	3.07 in
Dimension - Hole Size mm	78 mm
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.71 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	1.63 in

Dimension - Strip Length inch	1-5/8 in
Dimension - Stud Size inch	3/8 in
Dimension - Thread Size	3/8
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper DLO Size Range	777.7 kcmil(1925/24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex G Size Range	750 kcmil/FLEX
Conductor - Copper Flex H Size	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Solid Size	750 kcmil/FLEX
Conductor - Copper Str Size	750 kcmil/FLEX
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)