



## YA44L2NT38FX

by Burndy  
Catalog ID: YA44L2NT38FX

Prop 65 Notice

Copper Compression Lug, Narrow Tongue, 2 Hole w/ Inspection Window, 777.7 Flex, 3/8" Stud, 1" Stud Hole Spacing, Short Barrel, Tin - Electro Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Wire Strip Length: 1-5/8 IN, Tongue Angle: Straight, Finish: Electro-Tin Plated, Die Index: L115, Color Code: Yellow, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y35, Y39, Y750, PAT750 Tool, U44XRT Die, (2), Y46 Tool, U44XRT Die With PUADP-1 Adapter, (2), Conductor Type: Flexible Copper, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2)

## Product Details

### General

Application	For Flex Conductor
Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YA-L-2TC-FX, Standard Barrel
UPC	781810021422

### Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.03 in
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.74 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.50 in

Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	1-5/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper DLO Size Range	777.7 (1925/#24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex G Size Range	750
Conductor - Copper Flex H Size	750
Conductor - Copper Flex H Size Range	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex I Size Range	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex K Size Range	750
Conductor - Copper Flex M Size	750
Conductor - Copper Str Size	750
Conductor - Copper Str Size Range	750

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)