



## YA464N

by Burndy  
Catalog ID: YA464N

Prop 65 Notice

Copper Compression Lug, 4 Hole w/o Inspection Window, 1500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated.

Features: 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y46 Tool, P46RT Die, Color Code: Green, Die Index: 31, Wire Strip Length: 3-1/4 IN

## Product Details

### General

Application	For use on copper compression connections
Color Code	Green
Connector Type	Terminal
Die Index	31
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810086056
UPC 12 Digit	7818100860566

### Dimensions

Dimension - B Length inch	3.19 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.55 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	3.00 in
Dimension - Strip Length inch	3-1/4
Dimension - Stud Size inch	1/2

Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	1500 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)