

YA46TC58FXB

by Burndy
Catalog ID: YA46TC58FXB

Prop 65 Notice

Copper Compression Lug, 1 Hole w/o Inspection Window, 1111 Flex, 5/8" Stud, Long Barrel, Belled End, Tin Plated



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	29
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810086261
UPC 12 Digit	7818100862611

Dimensions

Dimension - B Length inch	3.58 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.19 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.98 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	3-11/16
Dimension - Stud Size inch	5/8
Dimension - Thread Size	5/8 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1111 (2750/#24)
Conductor - Copper Flex G Size	1111
Conductor - Copper Flex H Size	1111
Conductor - Copper Flex I Size	1111
Conductor - Copper Flex K Size	1111
Conductor - Copper Flex M Size	1111
Conductor - Copper Flex M Size Range	1111
Conductor - Copper Str Size	1000 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)